


TECHNICAL DATA SHEET

DESCRIPTION

The Aztec® E-Z Chair® - PEZ is used for Single Mat- Rebar or Wire Mesh, Bottom Layer Double Mat Rebar or Wire Mesh, Tilt-Wall, Side-Form Spacer, On-Grade: when used with Sand Plate.

PRODUCT SPECIFICATION

- Fits up to #8 Rebar
- Concrete gray color
- Meets all requirements and qualifies as a CRSI Class 1 Bar Support



Used for Chair Sizes up to 3" Cover Height.



Used for Chair Sizes for 3-1/4" to 6" Cover Height.

FEATURES

- Standard "Concrete Gray" color (custom colors available-inquire)
- Minimal surface contact
- Designed for maximum aggregate flow and concrete consolidation
- High load capacity
- Fits up to #8 rebar
- Does not straddle bottom rebar mat in double mat applications (for straddling applications, see Tower Chair or Straddle Chair)

ORDERING INFORMATION

AZTEC® E-Z CHAIR

Product Code	Description	Weight
127667	3/4" X #3 - 10MM TO #8 - 25MM	0.02 LB
127651	1" X #3 - 10MM TO #8 - 25MM	0.02 LB
127673	1-1/4" X #3 - 10MM TO #8 - 25MM	0.03 LB
127660	1-1/2" X #3 - 10MM TO #8 - 25MM	0.03 LB
127662	1-3/4" X #3 - 10MM TO #8 - 25MM	0.04 LB
127668	2" X #3 - 10MM TO #8 - 25MM	0.04 LB
127652	2-1/4" X #3 - 10MM TO #8 - 25MM	0.06 LB
127674	2-1/2" X #3 - 10MM TO #8 - 25MM	0.06 LB
127653	2-3/4" X #3 - 10MM TO #8 - 25MM	0.10 LB
127663	3" X #3 - 10MM TO #8 - 25MM	0.10 LB
127675	3-1/4" X #3 - 10MM TO #8 - 25MM	0.10 LB
127669	3-1/2" X #3 - 10MM TO #8 - 25MM	0.10 LB
127654	3-3/4" X #3 - 10MM TO #8 - 25MM	0.11 LB
127676	4" X #3 - 10MM TO #8 - 25MM	0.11 LB
127655	4-1/4" X #3 - 10MM TO #8 - 25MM	0.11 LB
127664	4-1/2" X #3 - 10MM TO #8 - 25MM	0.13 LB
127677	4-3/4" X #3 - 10MM TO #8 - 25MM	0.13 LB
127670	5" X #3 - 10MM TO #8 - 25MM	0.16 LB
127656	5-1/4" X #3 - 10MM TO #8 - 25MM	0.16 LB
127678	5-1/2" X #3 - 10MM TO #8 - 25MM	0.16 LB
127657	5-3/4" X #3 - 10MM TO #8 - 25MM	0.18 LB
127665	6" X #3 - 10MM TO #8 - 25MM	0.19 LB

MANUFACTURER

Dayton Superior Corporation
 1125 Byers Road
 Miamisburg, OH 45342
 Customer Service: 888-977-9600
 Technical Services: 877-266-7732
 Website: www.daytonsuperior.com

TECHNICAL DATA SHEET

WARRANTY (ACCESSORIES)

Limited Warranty. Dayton warrants, for a period of 60 days from the date of shipment (three years from the date of shipment in the case of formwork, excluding any consumable Products included with such formwork), that Products and any associated application drawings and engineering services provided by Dayton ("Ancillary Services") will be free from defects in material and workmanship and, in the case of custom designed formwork, that the formwork will meet the specifications set forth in the design drawings approved by Dayton and Customer. Any claim under this warranty must be made in writing within such warranty period. If any Product and/or Ancillary Service covered by a timely claim are found to be defective, Dayton will, within a reasonable time, make any necessary repairs or corrections or, at Dayton's option, replace the Product. Unless pre-authorized by Dayton in writing, Dayton will not accept any charges for correcting defects or accept the return of any Product. This warranty will not apply to any Products that have been subjected to misuse, neglect, storage damage, misapplication, accident or any other damage caused by any person other than Dayton, or that have not been maintained in accordance with Dayton's specifications. THIS LIMITED WARRANTY IS IN LIEU OF ALL OTHER WARRANTIES AS TO THE PRODUCTS AND ANCILLARY SERVICES. DAYTON MAKES NO OTHER WARRANTIES OR GUARANTEES, EXPRESS OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR OTHERWISE. THE REMEDIES SET FORTH IN THIS SECTION ARE CUSTOMER'S EXCLUSIVE REMEDY FOR BREACH OF WARRANTY.